

Combines four different technologies

RF+Vacuum+IR+ Ultrasound Cavitation 4 in 1



- ▶ Fat reduction
- ▶ Body contouring
- ▶ Cellulitis treatment
- ▶ Wrinkles removal
- ▶ Face lifting



PRODUCT INTRODUCTION



VACUUM RF HANDLE



Combination of Multi-polar RF, Vacuum & IR makes it possible to deliver RF energy to the desired target area effectively and precisely. Both face and body treatment is possible, offering a wide range of benefits such as anti-wrinkle and skin regeneration effect.



VACUUM RF HANDLE (L)



VACUUM RF HANDLE (M)



VACUUM RF HANDLE (S)




Equipped with three different sizes of treatment heads, used for facial and neck skin tightening and lifting, eye wrinkles removal, eye bags and dark circles treatment.




MILT-POLAR RF HANDLE



The combination of Multi-polar RF and IR enables accurate and effective RF energy transfer while improving skin elasticity.
3 size of handpieces allow various area treatment from face to whole body.



MILT-POLAR RF HANDLE (L)




MILT-POLAR RF HANDLE (M)



MILT-POLAR RF HANDLE (S)




ULTRASOUND CAVATION HANDLE




- ▶ 60Khz ultrasonic wave, directly reach the fat layer, the fat reduction effect is remarkable.
- ▶ 80mm diameter ultra-large ultrasonic array, provides better whole-body fat reduction effect, and faster treatment speed.






JAPAN SMC SOLENOID VALVE

High speed, long life, no noise



ITALY IMPORTED AIR PUMP

Large flow, low noise





AMERICA COHERENT IR LASER DIODE

High power, long life



JAPAN IMPORTED TRIPLE FREQUENCY RF POWER SUPPLY

It adopts triple frequency RF power supply imported from Japan, which can output three different frequencies of 1M, 5M and 8M respectively, and three different penetration depths. Customers can choose different frequencies for treatment according to different treatment items.



1M RF for body slimming, weight loss and body shaping

5M RF for deep wrinkles wrinkle removal, skin tightening and lifting

8M RF for superficial wrinkle removal and skin tightening





SPECIFICATIONS

Voltage	220V/110V
Power	500W
Vacuum	82KP
RF frequency	1MHz/5MHz/8MHz
Output mode	Continuous output
RF power	300W
Screen	12.1 inch Touch screen
Handle quantity	7 pieces